



Health Care Call System

Pushbutton Bath Station

Cat. 6146

DESCRIPTION

Jeron's Cat. 6146 Bath Stations are used to signal the Master Station from a bath or similar location where a pullcord is not needed or a patient must not have access to a cord.

- Modular
- For Pushbutton Activation of Bath Calls

OPERATION

Pressing the top of the button activates all system call signals for an urgent level call. The panel indicator illuminates to verify the call is placed.

Bath calls must be canceled at the originating bath station by pressing the bottom of the button.

EQUIPMENT

The Station is furnished with a call button, red call LED and 'PRESS FOR HELP' label on a modular red subplate for flush wall mount with included white trimplate or for ganging with other station subplates in a common opening by use of the 6802 adapter trimplate. The low profile pushbutton has a positive detent rocker action to resist accidental or partial operation. The panels resist common hospital cleaning agents.

The following accessory may be used:

- Cat. 9980 Water Resistant Gasket



ARCHITECTS/ENGINEERS SPECIFICATIONS

The Pushbutton Bath Station shall be the Jeron Cat. 6146 with a low profile pushbutton that has a positive detent action, and a red call placed LED on a modular red plastic subplate with a separate faceplate for flush wall mount. The bath calls shall be canceled at the originating Bath station only.

TECHNICAL DATA

Construction:

- Subplate: High-impact, flame-retardant molded ABS plastic with red color finish
- Trimplate: Thermoset, white color

Dimensions (H x W x D):

- 4.5 x 2.75 x 2.5 in.
(11.4 x 7 x 6.4 cm)

Back-box Required:

- Raco 670RAC 1-gang or equivalent mounted 1/2" behind wallface or Raco 232 2-gang with Raco 772 1-gang raised cover or equivalent

Controls/Indicators:

- Pushbutton: Black molded thermoplastic
- Call placed indicator: Red LED
- Label: 'PRESS FOR HELP' 1/8" block characters

Operating Voltage:

- 28 VDC

Field Connections:

- Plug-in IDC block; Connector provided

Certification:

- UL 1069 Listed
- C-UL — Canadian Standard C22.2 NO.125

PRODUCT SUBJECT TO CHANGE WITHOUT NOTIFICATION.