

## Code Station

Cat. 6149

### DESCRIPTION

Jeron's Cat. 6149 Code Stations are used in nurse call systems to allow staff members to call for immediate assistance. Code calls take precedence over all other call types.

- Modular

### OPERATION

Pressing the top of the button activates all system call signals for an emergency level call, the highest of three system call priority levels. The panel indicator illuminates to verify that the call has been placed. The code calls must be canceled at the originating Code station by pressing the bottom of the button.

### EQUIPMENT

The station is furnished with a call button, green call placed LED, and 'CODE' label on a modular blue plastic subplate for flush wall mount with the included white plastic trimplate or for ganging with the other station subplates in a common opening by use of the 6802 adapter trimplate. The low profile pushbutton has a positive detent rocker action to resist accidental or partial operation. The panels resist common hospital cleaning agents.



### ARCHITECTS/ENGINEERS SPECIFICATIONS

The Code Station shall be the Jeron Cat. 6149 with a low profile pushbutton that has a positive detent action, and a green call placed LED on a modular blue plastic subplate with a separate plastic faceplate for flush wall mount. The code calls shall be canceled at the originating station only.

### TECHNICAL DATA

#### Construction:

- Subplate: High-impact, flame-retardant molded ABS plastic with blue color finish
- Trimplate: Thermoset, white color

#### Dimensions (H x W x D):

- 4.5 x 2.75 x 2.5 in.  
(11.4 x 7 x 6.4 cm)

#### Back-box Required:

- Raco 670RAC 1-gang or equivalent mounted 1/2" behind wall face or Raco 232 2-gang with Raco 772 1-gang raised cover or equivalent

#### Controls/Indicators:

- Pushbutton: Black molded thermoplastic
- Call placed indicator: Green LED
- Label: 'CODE' 1/8" block characters

#### Operating Voltage:

- 28 VDC

#### Field Connections:

- Plug-in IDC block; Connector provided

#### Certification:

- UL 1069 Listed
- C-UL — Canadian Standard C22.2 NO.125

PRODUCT SUBJECT TO CHANGE WITHOUT NOTIFICATION.