



# Health Care Call System

## Visual Duty Station Cat. 6417

### DESCRIPTION

Jeron Visual Duty Stations are used to alert staff at remote locations that a call has been received at the Nurse Master Station.

- ❑ Three Separate Call Signals: Routine, Urgent, and Emergency
- ❑ Tone Silence

### OPERATION

When a call is placed on the system, the Duty Station duplicates the common signals that occur at the Nurse Master Station. The ROUTINE, URGENT, or EMERGENCY call status indicator illuminates and the corresponding alert tone sounds at the Visual Duty Station. Signals always indicate the highest level call currently on the system.

Alert tones can be momentarily silenced by pressing the TONE SILENCE button. Subsequent calls will reactivate the alert tones.

Alert tones may be preset at the time of the installation to high or low volume or muted.

### EQUIPMENT

The Visual Duty Station has indicators for routine, urgent, and emergency-level calls, as well as a TONE SILENCE button and an alert tone generator.



The Visual Duty Station is furnished on a one-gang modular subplate for flush wall mount with the included trimplate. Panels resist common hospital cleaning agents.

### ARCHITECTS/ENGINEERS SPECIFICATIONS

The Duty Station shall be Jeron Cat. 6417 equipped with ROUTINE, URGENT, and EMERGENCY call status LEDs and a TONE SILENCE button on a plastic faceplate with separate subplate for flush wall mounting.

Station shall be capable of duplicating all common call signals received at the Nurse Master Station.

Pressing the TONE SILENCE button shall silence the current call.

### TECHNICAL DATA

#### Mounting:

- White thermoset one-gang trimplate with separate modular subplate and matching plastic hardware

#### Dimensions (H x W x D):

- 4.5 x 2.75 x 2.5 in.  
(11.4 x 7 x 6.4 cm)

#### Back-box Required:

- Raco 670RAC 1-gang mounted 1/2" behind wall face *or* Raco 232 2-gang with Raco 772 1-gang raised cover

#### Controls/Indicators:

- Green ROUTINE call status LED indicator.
- Amber URGENT call status LED indicator.
- Red EMERGENCY call status LED indicator.
- TONE SILENCE pushbutton.
- Piezo-electric alert on generator.

#### Operating Voltage:

- 28 VDC

#### Field Connections:

- Plug-in IDC block

#### Certification:

- UL 1069 Listed
- C-UL — Canadian Standard C22.2 NO. 125

PRODUCT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION