

All-Call Interface Cat. 6847

DESCRIPTION

Jeron All-Call Interfaces are used to sound an all-call page through the speakers of patient or other remote stations.

- Simplifies Installation by Using Existing Speakers

EQUIPMENT

The All-Call Interface is furnished on a one-gang modular plastic subplate for flush wall mounting with a white plastic trimplate. Ganging with other station subplates in a common opening may be accomplished by the 6802-6806 Multi-gang Adapter Trimplates.

System equipment minimum requirements for All-Call Paging are: one UL 538 Listed paging amplifier of suitable capacity, one 6816 P.A. Page Control and one 6847 All-Call Interface for each remote station to receive the page.



ARCHITECTS/ENGINEERS SPECIFICATIONS

All-Call Interface shall be the Jeron Cat. 6847 mounted on a modular plastic subplate with the separate plastic subplate with separate plastic faceplate for flush wall mounting. It shall interface speakers in Jeron Remote Stations to a 25V output line of a UL 538 Listed paging amplifier.

TECHNICAL DATA

Mounting:

- White thermoset 1-gang trimplate with separate modular subplate and matching plastic hardware

Dimensions (H x W x D):

- 4.5 x 2.75 x 2.5 in.
(11.4 x 7 x 6.4 cm)

Back-box Required:

- Raco 670RAC 1-gang mounted 1/2" behind wall face *or* Raco 232 2-gang with Raco 772 1-gang raised cover

Operating Voltage:

- 28 VDC

Field Connections:

- Plug-in IDC block; connector provided

Audio Line Input/Output

- 25 VAC/45 Ohm

Certification:

- UL 1069 Listed
- C-UL — Canadian Standard C22.2 NO.125

PRODUCT SUBJECT TO CHANGE WITHOUT NOTIFICATION.